



Ecofit Ledtubes T8

LEDtube 600mm 8W 740 G HV

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<7
Color rendering index (CRI)	73
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	600 mm
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh


Ecofit Ledtubes T8

Product Data

Order product name	LEDtube 600mm 8W 740 G HV
Full product name	LEDtube 600mm 8W 740 G HV
Full product code	871869673214400
Order code	929001184741
Material Nr. (12NC)	929001184741


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696732144
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696732151

Dimensional drawing




Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 740 G HV	mm		mm	mm	mm	mm	mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 740 G HV




Light Distribution Diagram - LEDtube 600mm 8W 740 G HV


Spectral Power Distribution Colour - LEDtube 600mm 8W 740 G HV

Ecofit Ledtubes T8


Lifetime



Life Expectancy Diagram - LEDtube 600mm 8W 740 G HV



Life Expectancy Diagram - LEDtube 600mm 8W 740 G HV



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 G HV

Life Expectancy Diagram - LEDtube 600mm 8W 740 G HV

Lumen Maintenance Diagram - LEDtube 600mm 8W 740 G HV

Ecofit Ledtubes T8

