



Ecofit LED tubes T8 Mains

LEDtube 600mm 8W 765 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Starting time (nom.)	
Cap base	G13 [Medium Bi-Pin Fluorescent]		0.5 s
Main application	Industrial	Warm-up time to 60% light (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.5
Switching cycle	50000X	Voltage (Nom)	220-240 V
B50L70	15000 h		
Light Technical		Temperature	
Colour Code	765 [CCT of 6,500 K]	T ambient (max.)	45 °C
Lamp Luminous Flux 25°C EL (Nom)	800 lm	T ambient (min.)	-20 °C
Lamp Luminous Flux (Nom)	800 lm	T storage (max.)	65 °C
Colour Temperature, horizontal (Nom)	6500 K	T storage (min.)	-40 °C
Colour consistency	<7	T-Case maximum (nom.)	60 °C
Colour Rendering Index,horiz (Nom)	73		
LLMF at end of nominal lifetime (nom.)	70 %	Controls and Dimming	
		Dimmable	no
		Mechanical and Housing	
		Product length	600 mm
		Approval and Application	
		Energy efficiency label (EEL)	A+
Operating and Electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	8 W		
Lamp current (nom.)	70 mA		

Ecofit LED tubes T8 Mains


Energy-saving product	Yes
Suitable for accent lighting	No
Approval marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh

Product Data

Full product code	871869652507400
Order product name	LEDtube 600mm 8W 765 T8 AP C G

EAN/UPC – product	8718696525074
Order code	929001184808
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001184808
Net weight (piece)	0.124 kg



Dimensional drawing




TLED 600mm 2ft T8 8W-18W 6500K G13 ND

Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28	588.5	595.5	602.5	602.5	27.8
8W 765 T8 AP C G	mm	mm	mm	mm	mm	mm	mm

Photometric data



LEDtube 600mm 8W 765 T8 CN I G



Ecofit LED tubes T8 Mains

Lifetime

