



# Ecofit Ledtubes T8

## LEDtube 600mm 8W 765 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data

General Information		Power Factor (Nom)		0.5
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes	<b>Temperature</b>		
Nominal Lifetime (Nom)	15000 h	T-Ambient (Max)		45 °C
Switching Cycle	50000X	T-Ambient (Min)		-20 °C
<b>Light Technical</b>		T-Storage (Max)		65 °C
Color Code	765 [ CCT of 6500K]	T-Storage (Min)		-40 °C
Beam Angle (Nom)	240 °	T-Case Maximum (Nom)		60 °C
Luminous Flux (Nom)	800 lm	<b>Controls and Dimming</b>		
Color Designation	Cool Daylight	Dimmable		No
Correlated Color Temperature (Nom)	6500 K	<b>Mechanical and Housing</b>		
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Length		600 mm
Color Consistency	<7	<b>Approval and Application</b>		
Color Rendering Index (Nom)	73	Energy Efficiency Label (EEL)		A+
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product		Yes
<b>Operating and Electrical</b>		Suitable For Accent Lighting		No
Input Frequency	50 to 60 Hz	Approval Marks		RoHS compliance KEMA Keur certificate
Power (Nom)	8 W			
Starting Time (Nom)	0.5 s			
Warm Up Time to 60% Light (Nom)	0.5 s			

# Ecofit Ledtubes T8

Energy Consumption kWh/1000 h	8 kWh
<b>Product Data</b>	
Full product code	871869652507400
Order product name	LEDtube 600mm 8W 765 T8 AP C G
EAN/UPC - Product	8718696525074
Order code	929001184808

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001184808
Net Weight (Piece)	0.124 kg



## Dimensional drawing

A3

Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28	588.5	595.5	602.5	602.5	27.8
8W 765 T8 AP C	mm	mm	mm	mm	mm	mm	mm
G							


TLED 600mm 2ft T8 8W-18W 6500K G13 ND

## Photometric data



LEDtube 600mm 8W 765 T8 CN I G

LEDtube 1200mm 16W 765 T8 CN I G



LEDtube 600mm 8W G13 T8 765 800lm AP C G



# Ecofit Ledtubes T8

## Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

## Ecofit Ledtubes T8

