

Ecofit Ledtubes T8

LEDtube 600mm 8W 765 G HV

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Starting Time (Nom)		0.5 s
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.5
Switching Cycle	50,000	Voltage (Nom)		220 V
Lighting Technology	LED	Temperature		
EU RoHS compliant	Yes	Ambient temperature range		-20 °C to 45 °C
Light Technical		T-Case Maximum (Nom)		60 °C
Color Code	765 [CCT of 6500K]	Controls and Dimming		
Beam Angle (Nom)	240 degree(s)	Dimmable		No
Luminous Flux	800 lm	Mechanical and Housing		
Color Designation	Cool Daylight	Product Length		600 mm
Correlated Color Temperature (Nom)	6500 K	Bulb Shape		Tube, double-ended
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Approval and Application		
Color Consistency	<7	Energy Saving Product		Yes
Color rendering index (CRI)	73	Suitable For Accent Lighting		No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval Marks		RoHS compliance KEMA Keur certificate
Operating and Electrical		Energy Consumption kWh/1000 h		8 kWh
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Power Consumption	8 W			

Ecofit Ledtubes T8



Product Data	
Order product name	LEDtube 600mm 8W 765 G HV
Full product name	LEDtube 600mm 8W 765 G HV
Full product code	871869673216800
Order code	929001184841
Material Nr. (12NC)	929001184841

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696732168
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696732175

Dimensional drawing


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 765 G HV	mm		mm	mm	mm	mm	mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 765 G HV


Light Distribution Diagram - LEDtube 600mm 8W 765 G HV




Spectral Power Distribution Colour - LEDtube 600mm 8W 765 G HV

Ecofit Ledtubes T8


Lifetime




Life Expectancy Diagram - LEDtube 600mm 8W 765 G HV



Life Expectancy Diagram - LEDtube 600mm 8W 765 G HV



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 G HV



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 G HV

Ecofit Ledtubes T8

