



MASTER LEDtube EM/ Mains T8

Master LEDTube 1200 mm 18W 865 T8 I W

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

- -
- -

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,100 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	116.67 lm/W
Color Consistency	<6
Color rendering index (CRI)	82

LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	18 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	0.92
Voltage (Nom)	100-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	70 °C


MASTER LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	18 kWh

Dimensional drawing




Photometric data



Light Distribution Diagram - Master LEDTube 1200 mm 18W 865 T8 I W

Product Data	
Order product name	Master LEDTube 1200 mm 18W 865 T8 I W
Full product name	Master LEDTube 1200 mm 18W 865 T8 I W
Full product code	871869652406000
Order code	929001187812
Material Nr. (12NC)	929001187812
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696524060
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696524077



Product	D1	D2	A1	A2	A3
Master LEDTube 1200 mm 18W 865 T8 I W	25.6 mm	27.8 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm




Spectral Power Distribution Colour - Master LEDTube 1200 mm 18W 865 T8 I W

MASTER LEDtube EM/Mains T8


Lifetime




Life Expectancy Diagram - Master LEDTube 1200 mm 18W 865 T8 I W



Lumen Maintenance Diagram - Master LEDTube 1200 mm 18W 865 T8 I W



Life Expectancy Diagram - Master LEDTube 1200 mm 18W 865 T8 I W



Life Expectancy Diagram - Master LEDTube 1200 mm 18W 865 T8 I W

Lumen Maintenance Diagram - Master LEDTube 1200 mm 18W 865 T8 I W

MASTER LEDtube EM/Mains T8

