



# MASTER LEDbulb

## MASTER LEDbulb DT 11-75W A67 E27 827 FR

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

### Product data


General Information			
Cap base	E27 [ E27]	Lamp current (nom.)	63 mA
EU RoHS compliant	Yes	Wattage equivalent	75 W
Nominal lifetime (nom.)	25000 h	Starting time (nom.)	0.5 s
Switching cycle	50,000X	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	822-827 [ tunable warm white]	T-Case maximum (nom.)	100 °C
Lamp Luminous Flux 25°C EL (Nom)	1055 lm	Controls and Dimming	
Colour Designation	Warm white (WW)	Dimmable	Yes
Colour Temperature, horizontal (Nom)	- K	Approval and Application	
Lamp Luminous Efficacy EM (Nom)	96 lm/W	Energy efficiency label (EEL)	A+
Colour consistency	<6	Energy-saving product	Yes
Colour Rendering Index, horiz (Nom)	80	Suitable for accent lighting	No
LLMF at end of nominal lifetime (nom.)	70 %	Energy Consumption kWh/1000 h	11 kWh
Operating and Electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	11 W		

MASTER LEDbulb

Product Data	
Full product code	871869655551400
Order product name	MASTER LEDbulb DT 11-75W A67 E27 827 FR
EAN/UPC – product	8718696555514
Order code	55551400
Numerator – quantity per pack	1

Numerator – packs per outer box	6
Material no. (12NC)	929001200502
Net weight (piece)	0.131 kg


Dimensional drawing




Bulb 230V13W-75W 1055lm 300D 2700KE27 D

Product	D	C
MASTER LEDbulb DT 11-75W A67 E27 827 FR	70.6 mm	137.2 mm


Photometric data



LEDbulb 75W A67 2700K



LEDbulb 75W A67 2700K



LEDbulb 75W, 100W A67 2700K

## MASTER LEDbulb

