



CorePro LED PLC

CorePro LED PLC CorePro LED PLC 9W 830 4P G24q-3

Philips CorePro LED PLC is the ideal uplamping solution for downlights in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data


General Information		Power factor (nom.)	
Cap base	G24Q-3 [G24q-3]	0.9	
Nominal lifetime (nom.)	30000 h	Voltage (Nom)	
Switching cycle	50000X	20-50 V	
B50L70	30000 h		
Light Technical		Temperature	
Colour Code	830 [CCT of 3,000 K]	T ambient (max.)	
Lamp Luminous Flux 25°C EL (Nom)	950 lm	35 °C	
Lamp Luminous Flux (Nom)	950 lm	T ambient (min.)	
Colour Temperature, horizontal (Nom)	3000 K	-20 °C	
Colour consistency	<6	T storage (max.)	
Colour Rendering Index, horiz (Nom)	83	65 °C	
LLMF at end of nominal lifetime (nom.)	70 %	T storage (min.)	
		-40 °C	
		T-Case maximum (nom.)	
		76 °C	
Operating and Electrical		Controls and Dimming	
Input frequency	30000-80000 Hz	Dimmable	
Power (Rated) (Nom)	9 W	no	
Lamp current (max.)	400 mA		
Lamp current (min.)	250 mA	Mechanical and Housing	
Starting time (nom.)	0.5 s	Product length	
Warm-up time to 60% light (nom.)	0.5 s	200 mm	
		Approval and Application	
		Energy efficiency label (EEL)	
		A+	
		Energy-saving product	
		Yes	
		Approval marks	
		CE marking RoHS compliance KEMA Keur certificate	

CorePro LED PLC

Energy Consumption kWh/1000 h	12 kWh
Product Data	
Full product code	871869654115900
Order product name	CorePro LED PLC CorePro LED PLC 9W 830 4P G24q-3
EAN/UPC – product	8718696541159

Order code	929001200802
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001200802
Net weight (piece)	0.088 kg



Dimensional drawing




LEDtube PLC 9W G24q-3/830 4P

Product	D1	D2	A1	A2	A3
CorePro LED PLC CorePro LED PLC 9W 830 4P G24q-3	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm



Photometric data



LEDtube PLC 100mm 9W G24Q-3 830 950lm





Lifetime




LEDtube PLC 100mm 9W G24Q-3 830 950lm

LEDtube PLC 100mm 9W G24Q-3 830 950lm



LEDtube PLC 100mm 9W G24Q-3 830 950lm

LEDtube PLC 100mm 9W G24Q-3 830 950lm



LEDtube PLC 100mm 9W G24Q-3 830 950lm

