



MASTER LEDcandle DiamondSpark

MASTER LEDlustre DT 8-60W P50 E14 827 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	8-60W
Light Technical	
Colour code	822-827 [tunable warm white]
Luminous flux (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2200-2700 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6


Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	8 W
Lamp current (nom.)	45 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

MASTER LEDcandle DiamondSpark

Temperature	
T-Case maximum (nom.)	95 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869658067700
Order product name	MASTER LEDlustre DT 8-60W P50 E14 827 CL
EAN/UPC – product	8718696580677
Order code	58067700
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001211902
Net weight (piece)	0.084 kg


Dimensional drawing




Candle WG EMEA 60W E14 P50

Product	D	C
MASTER LEDlustre DT 8-60W P50 E14 827 CL	50 mm	111 mm

Photometric data




LED DimTone 8-60W 827



LED DimTone 8-60W 827 806lm

MASTER LEDcandle DiamondSpark

Photometric data



LEDlustrre 8-60W P50 827 806lm

