




A-Shape LED

6A19/LED/827-22/CL/DIM 120V

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux	480 lm
Color Designation	Warm Glow(WG)
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	ANSI 2700K
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	6 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s


Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A19 [A 19mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh
Energy Certifications	Energy Star
Product Data	
Order product name	6A19/LED/827-22/CL/DIM 120V
Full product name	6A19/LED/827-22/CL/DIM 120V
Order code	462515
Material Nr. (12NC)	929001215104

A-Shape LED

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677462512
Numerator - Packs per outer box	10


EAN/UPC - Case	50046677462517
----------------	----------------

Dimensional drawing




Product	D	C
6A19/LED/827-22/CL/DIM 120V	62 mm	111 mm


Photometric data




Spectral Power Distribution Colour - 6A19/LED/827-22/CL/DIM 120V



Spectral Power Distribution Colour - 6A19/LED/827-22/CL/DIM 120V



General uniform lighting - 6A19/LED/827-22/CL/DIM 120V



Light Distribution Diagram - 6A19/LED/827-22/CL/DIM 120V

A-Shape LED

