

**PHILIPS**

Eco passport

## Essential LED 4.6-50W GU10 827 36D Classic LEDspotMV

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.



### Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

#### Energy

- Dimmable: No
- Energy Efficiency Label (EEL): A+
- Luminous Efficacy (rated) (Nom): 85.90 lm/W
- Power (Rated) (Nom): 4.6 W

#### Circularity

- Nominal Lifetime (Nom): 15000 h

#### Packaging

- SAP Weight Paper Unit (Case): 0.230 kg
- SAP Weight Paper Unit (Piece): 0.012 kg

#### Substances

- EU REACH restrictions compliant: Yes
- EU RoHS compliant: Yes
- PVC policy compliant: Yes

#### Weight & Materials

- Net Weight (Piece): 0.038 kg

Energy efficiency ranking / External awards



Further reading at:  
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2020 Signify Holding. All rights reserved.