



# Classic LEDspotMV

## Essential LED 4.6-50W GU10 827 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	GU10 [ GU10]		39 mA
EU RoHS compliant	Yes	Wattage Equivalent	50 W
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
Technical Type	4.6-50W	Power Factor (Nom)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [ CCT of 2700K]	T-Case Maximum (Nom)	78 °C
Beam Angle (Nom)	36 °		
Luminous Flux (Nom)	395 lm	Controls and Dimming	
Luminous Intensity (Nom)	700 cd	Dimmable	No
Color Designation	Warm White (WW)		
Correlated Color Temperature (Nom)	2700 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	85.90 lm/W	Energy Efficiency Label (EEL)	A+
Color Consistency	<6	Suitable For Accent Lighting	Yes
Color Rendering Index (Nom)	80	Energy Consumption kWh/1000 h	5 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Product Data	
Input Frequency	50 to 60 Hz	Full product code	871869670059400
Power (Rated) (Nom)	4.6 W	Order product name	Essential LED 4.6-50W GU10 827 36D
		EAN/UPC - Product	8718696700594

# Classic LEDspotMV

Order code	929001215208
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001215208

Net Weight (Piece)	0.038 kg
--------------------	----------



## Dimensional drawing



LEDClassic 50W GU10 WW 230V 36D ND 1BC/6

Product	D	C
Essential LED 4.6-50W GU10 827 36D	50 mm	54 mm


## Photometric data



Product Reference: 51, Photo Lighting: 51, Page: 10

LEDspotMV GU10 MR16 827


LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D




LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D

# Classic LEDspotMV

## Lifetime



CLA LEDspotMV 50W GU10 827 36D ND



CLA LEDspotMV 50W GU10 827 36D ND

