

PHILIPS

Eco passport

Essential LED 4.6-50W GU10 830 36D Classic LEDspotMV

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.



Our Eco passport



Energy

- Dimmable: No
- Energy efficiency label (EEL): A+
- Lamp Luminous Efficacy EM (Nom): 89.10 lm/W
- Power (Rated) (Nom): 4.6 W




Circularity

- Nominal lifetime (nom.): 15000 h



Packaging

- SAP Weight Paper Unit (Case): 0.230 kg
- SAP Weight Paper Unit (Piece): 0.012 kg



Substances

- EU RoHS compliant: Yes
- RoHS mark: RoHS mark



Weight & Materials

- Net weight (piece): 0.038 kg

Energy efficiency ranking / External awards

