

PHILIPS

Eco passport

Essential LED 4.6-50W GU10 830 36D Classic LEDspotMV

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** No
- **Lamp Luminous Efficacy EM (Nom):** 89.10 lm/W
- **Power (Rated) (Nom):** 4.6 W



Circularity

- **Nominal lifetime (nom.):** 15000 h



Packaging

- **SAP Weight Paper Unit (Case):** 0.230 kg
- **SAP Weight Paper Unit (Piece):** 0.012 kg



Substances

- **EU RoHS compliant:** Yes



Weight & Materials

- **SAP net weight (piece):** 0.038 kg

Further reading at:

<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2021 Signify Holding. All rights reserved.