



Classic LEDspotMV

Essential LED 4.6-50W GU10 830 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	4.6-50W
Light Technical	
Colour Code	830 [CCT of 3,000 K]
Technical Beam Angle (Nom)	36 °
Lamp Luminous Flux 25°C EL (Nom)	410 lm
Lamp Luminous Flux (Nom)	410 lm
Luminous intensity (nom.)	740 cd
Colour Designation	White (WH)
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	89.10 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4.6 W


Lamp current (nom.)	39 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869671342600
Order product name	Essential LED 4.6-50W GU10 830 36D
EAN/UPC – product	8718696713426

Classic LEDspotMV

Order code	929001218108
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001218108

Net weight (piece)	0.038 kg
--------------------	----------



Dimensional drawing



GU10 230V 4W-35W 260lm 100D 2700K GU10ND

Product	D	C
Essential LED 4.6-50W GU10 830 36D	50 mm	54 mm


Photometric data



Essential Ledspot MV 11W 900lm 3000K

LEDspot,PAR38 11W 900lm 3000K

CorePro LEDspotMV 50W GU10 830 36D CLA




CorePro LEDspotMV 50W GU10 830 36D CLA

Classic LEDspotMV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND



CLA LEDspotMV 50W GU10 827 36D ND

