



Classic LEDspotMV

CorePro LEDspot 5-50W GU10 827 36D DIM

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Product data

General Information	
Cap-Base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	5-50W
Light Technical	
Colour Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	350 lm
Luminous Intensity (Nom)	650 cd
Colour Designation	Warm White (WW)
Colour Temperature, horizontal (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<6
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	350 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz


Power (Rated) (Nom)	5 W
Lamp Current (Nom)	30 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869672137700
Order product name	CorePro LEDspot 5-50W GU10 827 36D DIM

Classic LEDspotMV

EAN/UPC - Product	8718696721377
Order code	72137700
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001218832
Net Weight (Piece)	0.036 kg


Dimensional drawing




GU10 230V 5W-50W 385lm 60D 3000K GU10 ND

Product	D	C
CorePro LEDspot 5-50W GU10 827 36D DIM	50 mm	53 mm


Photometric data



LEDspotMV GU10 MR16 827



LEDspotMV 5.5W-50W GU10 827 36D



Technical drawing of the LEDspotMV 5.5W-50W GU10 827 36D

LEDspotMV 5.5W-50W GU10 827 36D

Classic LEDspotMV

