



Classic filament LEDbulbs

LEDClassic 4.5-50W B35 E14 WW CL D APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4.5-50W
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	470 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	104.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4.5 W
Lamp current (nom.)	29 mA


Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869657475100

Classic filament LEDbulbs

Order product name	LEDClassic 4.5-50W B35 E14 WW CL D APR
EAN/UPC – product	8718696574751
Order code	929001227208
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001227208
Net weight (piece)	0.024 kg


Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E14D

Product	D	C
LEDClassic 4.5-50W B35 E14 WW CL D APR	35 mm	118 mm


Photometric data



LED Lamps, Lightcolour /827 D CL



Classic LEDCandle D 4.5-40W B35 827 CL



Classic LEDCandle D 4.5-40W B35 827 CL

Classic filament LEDbulbs

