



Classic filament LEDbulbs

LEDClassic 4.5-50W P45 E27 WW CL D APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)		29 mA
Cap-Base	E27 [E27]	Wattage Equivalent		50 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	20,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	15 hour(s)	Power Factor (Fraction)		0.7
Lighting Technology	LED	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)		70 °C
Luminous Flux	470 lm	Controls and Dimming		
Color Designation	Warm White (WW)	Dimmable		Yes
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	104.00 lm/W	Bulb Finish		Clear
Color Consistency	<6	Bulb Shape		P45 [P 45mm]
Color rendering index (CRI)	80	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h		5 kWh
Operating and Electrical		Product Data		
Line Frequency	50 to 60 Hz	Order product name		LEDClassic 4.5-50W P45 E27 WW CL D APR
Input Frequency	50 to 60 Hz			
Power Consumption	4.5 W			

Classic filament LEDbulbs

Full product name	LEDClassic 4.5-50W P45 E27 WW CL D APR
Full product code	871869657481200
Order code	929001227608
Material Nr. (12NC)	929001227608
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718696574812
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574829

Dimensional drawing




Product	D	C
LEDClassic 4.5-50W P45 E27 WW CL D APR	45 mm	89 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 4.5-50W P45 E27 WW CL D APR



General uniform lighting - LEDClassic 4.5-50W P45 E27 WW CL D APR



Light Distribution Diagram - LEDClassic 4.5-50W P45 E27 WW CL D APR

Classic filament LEDbulbs

