

Classic filament LEDbulbs

LEDClassic 7.5-70W A60 E27 WW CL D APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E27 [E27]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	7.5 W
Switching Cycle	20,000	Lamp Current (Nom)	40 mA
Rated Lifetime (Hours)	15,000 hour(s)	Wattage Equivalent	70 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	70 °C
Luminous Flux	806 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	107.00 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Shape	A60 [A 60mm]
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	LEDClassic 7.5-70W A60 E27 WW CL D APR
Full product name	LEDClassic 7.5-70W A60 E27 WW CL D APR
Full product code	871869657473700


Order code	929001228008
Material Nr. (12NC)	929001228008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574737
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696574744

Dimensional drawing




Product	D	C
LEDClassic 7.5-70W A60 E27 WW CL D APR	60 mm	112 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 7.5-70W A60 E27 WW CL D APR



General uniform lighting - LEDClassic 7.5-70W A60 E27 WW CL D APR



Light Distribution Diagram - LEDClassic 7.5-70W A60 E27 WW CL D APR

Classic filament LEDbulbs

