

Classic filament LEDbulbs

LEDClA 7.5-60W A60 E27 2000K GOLD APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)		42 mA
Cap-Base	E27 [E27]	Wattage Equivalent		60 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	20,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)		0.7
Lighting Technology	LED	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	820 [CCT of 2000K]	T-Case Maximum (Nom)		70 °C
Luminous Flux	600 lm	Controls and Dimming		
Color Designation	Flame	Dimmable		Yes
Correlated Color Temperature (Nom)	2000 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	80.00 lm/W	Bulb Finish		Gold Clear
Color Consistency	<6	Bulb Shape		A60 [A 60mm]
Color rendering index (CRI)	80	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product		Yes
Operating and Electrical		Suitable For Accent Lighting		No
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h		8 kWh
Input Frequency	50 to 60 Hz			
Power Consumption	7.5 W			

Classic filament LEDbulbs

Product Data	
Order product name	LEDClA 7.5-60W A60 E27 2000K GOLD APR
Full product name	LEDClA 7.5-60W A60 E27 2000K GOLD APR
Full product code	871869657483600
Order code	929001228108
Material Nr. (12NC)	929001228108


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574836
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696574843

Dimensional drawing




Product	D	C
LEDClA 7.5-60W A60 E27 2000K GOLD APR	60 mm	112 mm


Photometric data



Spectral Power Distribution Colour - LEDClA 7.5-60W A60 E27 2000K GOLD APR



General uniform lighting - LEDClA 7.5-60W A60 E27 2000K GOLD APR



Light Distribution Diagram - LEDClA 7.5-60W A60 E27 2000K GOLD APR

Classic filament LEDbulbs

