

# Decorative LED bulbs

## CLA LEDBulb D 7-50W ST64 B22 820 GOLD

The new Deco collection transforms your home with a perfect blend of warm white light and a lean, minimalistic lighting experience. With long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

### Product data

General Information	
Cap base	B22 [ B22]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7-50W

Light Technical	
Colour code	820 [ CCT of 2,000 K]
Luminous flux (nom.)	630 lm
Colour designation	Flame
Correlated colour temperature (nom.)	2000 K
Luminous efficacy (rated) (nom.)	90.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W
Lamp current (nom.)	40 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V


Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	7 kWh

Product Data	
Full product code	871869658107000
Order product name	CLA LEDBulb D 7-50W ST64 B22 820 GOLD
EAN/UPC – product	8718696581070
Order code	58107000
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001228402
Net weight (piece)	0.060 kg

# Decorative LED bulbs



## Dimensional drawing



filament 7W-60W 620lm NAD 2200K E27D


Product	D	C
CLA LEDBulb D 7-50W ST64 B22 820 GOLD	64 mm	146.5 mm

## Photometric data



LED Lamps, Lightcolour /820 ST64 GOLD

Classic LEDBulb D 7-50W ST64 820 GOLD



Classic LEDBulb D 7-50W ST64 820 GOLD

