



Classic filament LEDbulbs

LEDClassic 7-70W ST64 E27 WW CL D APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.


Product data

General Information		Lamp Current (Nom)		40 mA
Cap-Base	E27 [E27]	Wattage Equivalent		70 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	20,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)		0.7
Lighting Technology	LED	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)		70 °C
Luminous Flux	806 lm	Controls and Dimming		
Color Designation	Warm White (WW)	Dimmable		Yes
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	115.00 lm/W	Bulb Finish		Clear
Color Consistency	<6	Bulb Shape		ST64
Color rendering index (CRI)	80	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product		Yes
Operating and Electrical		Suitable For Accent Lighting		No
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h		7 kWh
Input Frequency	50 to 60 Hz			
Power Consumption	7 W			


Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 7-70W ST64 E27 WW CL D APR
Full product name	LEDClassic 7-70W ST64 E27 WW CL D APR
Full product code	871869657487400
Order code	929001228608
Material Nr. (12NC)	929001228608

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - LEDClassic 7-70W ST64 E27 WW CL D APR

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574874
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574881

Product	D	C
LEDClassic 7-70W ST64 E27 WW CL D APR	64 mm	148 mm



General uniform lighting - LEDClassic 7-70W ST64 E27 WW CL D APR



Light Distribution Diagram - LEDClassic 7-70W ST64 E27 WW CL D APR

Classic filament LEDbulbs

