



Classic filament LEDbulbs

LEDClassic 7-60W G120 E27 2000K GOLD APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Input Frequency	
Cap-Base	E27 [E27]	Power Consumption	7 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	40 mA
Switching Cycle	20,000	Wattage Equivalent	60 W
Rated Lifetime (Hours)	15,000 hour(s)	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.7
Light Technical		Voltage (Nom)	220-240 V
Color Code	820 [CCT of 2000K]	Temperature	
Luminous Flux	630 lm	T-Case Maximum (Nom)	70 °C
Color Designation	Flame	Controls and Dimming	
Correlated Color Temperature (Nom)	2000 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Gold Clear
Color rendering index (CRI)	80	Bulb Shape	G120 [G 120mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	LEDClassic 7-60W G120 E27 2000K GOLD APR
Full product name	LEDClassic 7-60W G120 E27 2000K GOLD APR


Full product code	871869657493500
Order code	929001229108
Material Nr. (12NC)	929001229108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574935
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574942

Dimensional drawing




Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm

Photometric data




Spectral Power Distribution Colour – LEDClassic 7-60W G120 E27 2000K GOLD APR



General uniform lighting – LEDClassic 7-60W G120 E27 2000K GOLD APR

Classic filament LEDbulbs

Photometric data



Light Distribution Diagram - LEDClassic 7-60W G120 E27 2000K GOLD APR

