



# Classic filament LEDbulbs

## LEDClassic 4-50W ST64 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4-50W
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	470 lm
Lamp Luminous Flux (Nom)	470 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	118.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W

Lamp current (nom.)	33 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	4 kWh


# Classic filament LEDbulbs

## Product Data

Full product code	871869657423200
Order product name	LEDClassic 4-50W ST64 E27 WW CL ND APR
EAN/UPC – product	8718696574232
Order code	929001237308
Numerator – quantity per pack	1

Numerator – packs per outer box	6
Material no. (12NC)	929001237308
Net weight (piece)	0.048 kg



## Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
LEDClassic 4-50W ST64 E27 WW CL ND APR	64 mm	140 mm

## Photometric data



CorePro LEDbulb ND 4-40W ST64 827



## Classic filament LEDbulbs

