



Classic filament LEDbulbs

CLA LED bulb ND 4-40W B22 827 A60 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4-40W

Light Technical	
Colour code	827 [CCT of 2,700 K]
Luminous flux (nom.)	470 lm
Luminous flux (rated) (nom.)	470 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	118.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W

Lamp current (nom.)	33 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy efficiency label (EEL)	A++
Energy Consumption kWh/1000 h	4 kWh


Product Data	
Full product code	871869676868600
Order product name	CLA LED bulb ND 4-40W B22 827 A60 CL

Classic filament LEDbulbs

EAN/UPC – product	8718696768686
Order code	76868600
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001237502
Net weight (piece)	0.030 kg



Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K B22ND

Product	D	C
CLA LED bulb ND 4-40W B22 827 A60 CL	60 mm	102 mm

Photometric data




CLA LEDbulb 40W B22 827 CL A60 ND



Classic filament LEDbulbs

Lifetime



LEDbulb 60W E14 827 FR B38

LEDbulb 60W E14 827 FR B38

