



MASTER LEDspot ExpertColor LV

MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 24D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data

General Information	
Cap base	GU5.3 [GU5.3]
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Technical type	7.2-50W
Light Technical	
Colour Code	930 [CCT of 3,000 K]
Technical Beam Angle (Nom)	24°
Lamp Luminous Flux 25°C EL (Nom)	480 lm
Luminous intensity (nom.)	2400 cd
Colour Designation	White (WH)
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	66.67 lm/W
Colour consistency	<3
Colour Rendering Index,horiz (Nom)	97

LLMF at end of nominal lifetime (nom.) 70 %	
Operating and Electrical	
Power (Rated) (Nom)	7.2 W
Lamp current (nom.)	800 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case maximum (nom.)	92 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application


Energy-saving product	Yes
Suitable for accent lighting	Yes

Product Data

Full product code	694793912155700
Order product name	MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 24D

EAN/UPC – product	6947939121557
Order code	929001242310
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001242310
Net weight (piece)	0.034 kg


Dimensional drawing




MR16 12V 7.2-50W 420lm 24D 3000K GU5.3 D

Product	D	C
MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 24D	51 mm	46 mm

Photometric data




MAS LED ExpertColor 7.2-50W MR16 GU5.3 930



MAS LED ExpertColor 7.2-50W MR16 GU5.3 930 24D

MASTER LEDspot ExpertColor LV

Photometric data



MAS LED ExpertColor 7.2-50W MR16 GU5.3 930 24D

