



CorePro LEDlinear MV

CorePro LED linear R7S 118mm 14-100W 840 D

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Product data

General Information	
Cap-Base	R7s
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	128.57 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	14 W
Lamp Current (Nom)	74 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Shape	Linear

Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes

CorePro LEDlinear MV


Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	465217
EyeComfort	Yes
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	CorePro R7S 118mm 14-100W 840 D
Full product name	CorePro LED linear R7S 118mm 14-100W 840 D

Full product code	871869657881000
Order code	57881000
Material Nr. (12NC)	929001243802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696578810
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696578827


Dimensional drawing

Product	D	C
CorePro R7S 118mm 14-100W 840 D	29 mm	118 mm

Photometric data




Spectral Power Distribution Colour - CorePro R7S 118mm 14-100W 840 D



General uniform lighting - CorePro R7S 118mm 14-100W 840 D

Photometric data



Light Distribution Diagram - CorePro R7S 118mm 14-100W 840 D

