



# MASTER LEDspot LV AR111

## MAS LEDspotLV D 11-50W 927 AR111 8D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

### Product data


General Information		Operating and Electrical	
Cap-Base	G53 [G53]	Luminous Efficacy (rated) (Nom)	54.55 lm/W
Nominal lifetime	40,000 hour(s)	Color Consistency	<3
Switching Cycle	50,000	Color rendering index (CRI)	90
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes		
Light Technical		Line Frequency	- Hz
Color Code	927	Input Frequency	- Hz
Beam Angle (Nom)	8 degree(s)	Power Consumption	11 W
Luminous Flux	600 lm	Lamp Current (Nom)	1,300 mA
Luminous Intensity (Nom)	7,800 cd	Wattage Equivalent	50 W
Color Designation	Warm White (WW)	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	2700 K	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7

## MASTER LEDspot LV AR111

Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	AR111
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	13 kWh



Product Data	
Order product name	MAS LEDspotLV D 11-50W 927 AR111 8D
Full product name	MAS LEDspotLV D 11-50W 927 AR111 8D
Full product code	871869670725800
Order code	70725800
Material Nr. (12NC)	929001243908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707258
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696707265

## Dimensional drawing



Product	D	C
MAS LEDspotLV D 11-50W 927 AR111 8D	111 mm	62 mm

## Photometric data



General uniform lighting - MAS LEDspotLV D 11-50W 927 AR111 8D

**Light Distribution Diagram - MAS LEDspotLV D 11-50W 927 AR111 8D**


# MASTER LEDspot LV AR111

## Photometric data




Spectral Power Distribution Colour - MAS LEDspotLV D 11-50W 927 AR111 8D

## Lifetime



Life Expectancy Diagram - MAS LEDspotLV D 11-50W 927 AR111 8D



Lumen Maintenance Diagram - MAS LEDspotLV D 11-50W 927 AR111 8D

