



Premium LED bulbs SceneSwitch

BC9A19/AMB/850/ND SSDL 120V 4/1

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LED bulbs, adapt your room ambiance to suit whatever you're doing, by changing the setting from cool day light to warm white, or dimming the brightness. All you need is your existing switch no extra installation is required.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	100000X
Technical Type Setting(s)	9/3/1-60 W
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	300 °
Luminous Flux Setting(s)	800/320/80 lm
Luminous Flux (Rated) Setting(s)	800/320/80 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Correlated Color Temperature Setting(s)	5000 K
Luminous Efficacy (rated) (Nom)	89.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) Setting(s)	9/3/1 W
Lamp Current (Nom)	130 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.6
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted


Premium LED bulbs SceneSwitch

Product Data

XUCDM.COPY.Product.Title	BC9A19/AMB/850/ND SSDL 120V
EAN/UPC - Product	046677464905
Order code	464909
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	4
Material Nr. (12NC)	929001261403
Net Weight (Piece)	0.130 kg


Dimensional drawing




Scce-Switch Bulb A19 120V 5000K E26 ND

Product	D	C
BC9A19/AMB/850/ND SSDL 120V	61.0 mm	111 mm

Photometric data



SceneSwitch Bulb 60W A19 800lm 5000K 120V ND



SceneSwitch Bulb 60W A19 800lm 5000K 120V ND

