

Classic filament LEDbulbs

LED B35 1-25W E14 CL ND 830

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	200.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	1 W
Lamp Current (Nom)	10 mA


Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	1 kWh

Classic filament LEDbulbs

Product Data	
Order product name	LED B35 1-25W E14 CL ND 830
Full product name	LED B35 1-25W E14 CL ND 830
Full product code	871869665885700
Order code	65885700
Material Nr. (12NC)	929001262402


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696658857
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696658864

Dimensional drawing




Product	D	C
LED B35 1-25W E14 CL ND 830	35 mm	97 mm


Photometric data



General uniform lighting - LED B35 1-25W E14 CL ND 830



Light Distribution Diagram - LED B35 1-25W E14 CL ND 830



Spectral Power Distribution Colour - LED B35 1-25W E14 CL ND 830

Classic filament LEDbulbs

