



A-Shape LED

BC10A19/AMB/927/DIM 120V

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	927
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	10 W
Lamp Current (Nom)	100 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	85 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19 [A 19mm]


Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	- kWh

Product Data	
Order product name	BC10A19/AMB/927/DIM 120V
Full product name	BC10A19/AMB/927/DIM 120V
Order code	929001263303
Material Nr. (12NC)	929001263303
Numerator - Quantity Per Pack	1

A-Shape LED



EAN/UPC - Product/Case	046677465186
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677465181

Dimensional drawing




Product	D	C
BC10A19/AMB/927/DIM 120V	61.4 mm	109.8 mm

Photometric data



Spectral Power Distribution Colour - BC10A19/AMB/927/DIM 120V



General uniform lighting - BC10A19/AMB/927/DIM 120V

Light Distribution Diagram - BC10A19/AMB/927/DIM 120V

A-Shape LED

