



Standard LED bulbs

LEDBulb 23W E27 6500K 100-240V A110 ARG

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Wattage Equivalent	
Cap-Base	E27 [E27]	200 W	
Nominal lifetime	25,000 hour(s)	Starting Time (Nom)	
Switching Cycle	50,000	0.9 s	
Lighting Technology	LED	Warm-up time to 60% light	
EU RoHS compliant	Yes	0.5 s	
Light Technical		Power Factor (Fraction)	
Color Code	865 [CCT of 6500K]	0.7	
Beam Angle (Nom)	150 degree(s)	Voltage (Nom)	
Luminous Flux	3,000 lm	100-240 V	
Color Designation	Cool Daylight	Temperature	
Correlated Color Temperature (Nom)	6500 K	T-Case Maximum (Nom)	
Luminous Efficacy (rated) (Nom)	130.43 lm/W	85 °C	
Color Consistency	<6	Controls and Dimming	
Color rendering index (CRI)	80	Dimmable	
LLMF At End Of Nominal Lifetime (Nom)	70 %	No	
Operating and Electrical		Mechanical and Housing	
Line Frequency	50 to 60 Hz	Bulb Finish	
Input Frequency	50 to 60 Hz	Frosted	
Power Consumption	23 W	Bulb Shape	
		A110 [A 110mm]	
		Approval and Application	
		Energy Consumption kWh/1000 h	
		23 kWh	
		Product Data	
		Order product name	
		LEDBulb 23W E27 6500K 100-240V A110 ARG	
		Full product name	
		LEDBulb 23W E27 6500K 100-240V A110 ARG	

Standard LED bulbs

Full product code	871869666002700
Order code	929001269012
Material Nr. (12NC)	929001269012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696660027

Numerator - Packs per outer box	6
EAN/UPC - Case	8718696660034

Dimensional drawing



Product	D	C
LEDBulb 23W E27 6500K 100-240V A110 ARG	110 mm	204 mm

