



Ecofit Ledtubes T8

Ecofit LEDtube 600mm 8W 865 T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Light Technical	
Colour Code	865 [CCT of 6500K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	800 lm
Colour Temperature, horizontal (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	8 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5

Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	600 mm
Approval and Application	
Energy Efficiency Label	A+
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh

Ecofit Ledtubes T8

Product Data

Full product code	871869959528900
Order product name	Ecofit LEDtube 600mm 8W 865 T8
EAN/UPC - Product	8718699595289
Order code	59528900
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001276302
Net Weight (Piece)	0.120 kg



Dimensional drawing

A3


Product	D1	D2	A1	A2	A3
Ecofit LEDtube 600mm 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

TLED Ecofit EU 600mm 8W 800lm 6500K

Photometric data



LEDtube Ecofit 16W G13 840 24D ND





LEDtube Ecofit 8W G13 865 24D ND

LEDtube Ecofit 16W G13 865 24D ND



Ecofit Ledtubes T8

Lifetime




LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

Ecofit Ledtubes T8

