

Ecofit Ledtubes T8



Ecofit LEDtube 600mm 8W 865 T8 I

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		8 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
Flux measurement reference	Sphere	Voltage (Nom)	220-240 V
EU RoHS compliant	Yes	Temperature	
Light Technical		Ambient temperature range	-20 °C to 45 °C
Color Code	865 [CCT of 6500K]	T-Case Maximum (Nom)	55 °C
Beam Angle (Nom)	240 degree(s)	Controls and Dimming	
Luminous Flux	800 lm	Dimmable	No
Color Designation	Cool Daylight	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Bulb Material	Glass
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Length	600 mm
Color Consistency	<6	Bulb Shape	T8
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Class	F
Operating and Electrical		Energy Saving Product	Yes
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Ecofit Ledtubes T8


Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	491858
Product Data	
Order product name	Ecofit LEDtube 600mm 8W 865 T8 I
Full product name	Ecofit LEDtube 600mm 8W 865 T8 I
Full product code	871869969706800

Order code	69706800
Material Nr. (12NC)	929001276322
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699697068
Numerator - Packs per outer box	20
EAN/UPC - Case	8718699697075


Dimensional drawing

Product	D1	D2	A1	A2	A3
Ecofit LEDtube 600mm 8W 865 T8 I	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


Photometric data



Light Distribution Diagram - Ecofit LEDtube 600mm 8W 865 T8 I




General uniform lighting - Ecofit LEDtube 600mm 8W 865 T8 I




Spectral Power Distribution Colour - Ecofit LEDtube 600mm 8W 865 T8 I

Ecofit Ledtubes T8


Lifetime




Lumen Maintenance Diagram - Ecofit LEDtube 600mm 8W 865 T8 I




Lumen Maintenance Diagram - Ecofit LEDtube 600mm 8W 865 T8 I



Life Expectancy Diagram - Ecofit LEDtube 600mm 8W 865 T8 I



Life Expectancy Diagram - Ecofit LEDtube 600mm 8W 865 T8 I



Life Expectancy Diagram - Ecofit LEDtube 600mm 8W 865 T8 I

Ecofit Ledtubes T8

