



MASTER Value Decorative LED bulbs

LED Classic CM A60 30W WW E27 CL ND SRT4

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	370 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	105.71 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	33 mA
Wattage Equivalent	30 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C

MASTER Value Decorative LED bulbs

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
EyeComfort	Yes
Product Data	
Order product name	LED Classic CM A60 30W WW E27 CL ND SRT4


Full product name	LED Classic CM A60 30W WW E27 CL ND SRT4
Full product code	871869666867201
Order code	929001276458
Material Nr. (12NC)	929001276458
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696668672
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696729779

Dimensional drawing




Product	D	C
LED Classic CM A60 30W WW E27 CL ND SRT4	60 mm	104 mm

Photometric data




Spectral Power Distribution Colour - LED Classic CM A60 30W WW E27 CL ND SRT4



Light Distribution Diagram - LED Classic CM A60 30W WW E27 CL ND SRT4


MASTER Value Decorative LED bulbs

Photometric data




General uniform lighting - LED Classic CM A60 30W WW E27 CL ND SRT4

Lifetime



Life Expectancy Diagram - LED Classic CM A60 30W WW E27 CL ND SRT4



Lumen Maintenance Diagram - LED Classic CM A60 30W WW E27 CL ND SRT4

