



Essential LEDtube

LEDtube HO 1200mm 20W 740 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Light Technical	
Color Code	740 [CCT of 4000K]
Luminous Flux (Nom)	2100 lm
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<7
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	20 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220–240 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	65 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	1200 mm

Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh

Product Data	
Full product code	871869667434500
Order product name	LEDtube HO 1200mm 20W 740 T8 AP I G
EAN/UPC - Product	8718696674345

Essential LEDtube

Order code	929001277208
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001277208

Net Weight (Piece)	0.215 kg
--------------------	----------



Dimensional drawing

A3

Product	D1	D2	A1	A2	A3
LEDtube HO 1200mm 20W 740 T8 AP I G	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


TLED Ecofit APR HO 1200mm 4ft T8 220-240

Photometric data



LEDtube HO 20W G13 740 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 740 T8 AP I G



Essential LEDtube

Lifetime




LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

Essential LEDtube

