



T5

24T5HO/46-835/IF33/P/DIM 10/1

Philips LED T5 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Product data

General Information	
Base	G5 [G5]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X

Light Technical	
Color Code	835 [CCT of 3500K]
Initial lumen (Nom)	3300 lm
Correlated Color Temperature (Nom)	3500 K
Color Consistency	<5
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	40000-80000 Hz
Power (Rated) (Nom)	24 W
Lamp Current (Max)	600 mA
Lamp Current (Min)	400 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	39-64 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Product Length	1200 mm


Approval and Application	
Energy Saving Product	Yes
Approbation Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard

Product Data	
Order product name	24T5HO/46-835/IF33/P/DIM 10/1
EAN/UPC - Product	046677467135
Order code	467134
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001283804

T5

Net Weight (Piece)	0.170 kg
Model Number	9290012838



Dimensional drawing



TLED 120V 24-54W 3600lm 3500K G5

Product	D1	D2	A1	A2	A3
24T5HO/46-835/ IF33/P/DIM 10/1	15.2 mm	17.8 mm	1147.8 mm	1154.9 mm	1162 mm


Photometric data



General Information Light 2019
© 2019 Philips Lighting B.V.

LEDtube 1100mm 24W G5 835 3300lm

LEDtube 1100mm 24W G5 835 3300lm



LEDtube 1100mm 24W G5 835 3300lm

