

17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM LED PAR38

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: Yes
- Energy Efficiency Label (EEL): Not applicable
- Luminous Efficacy (rated) (Nom): 70 lm/W
- Power (Rated) (Nom): 17 W



• Nominal Lifetime (Nom): 40000 h



- SAP Weight Paper Unit (Case): 0.972 kg
- SAP Weight Paper Unit (Piece): 0.112 kg



- EU REACH restrictions compliant: Yes
- EU RoHS compliant: Yes



• Net Weight (Piece): 0.425 kg