



MASTER LEDtube EM/ Mains T8

MASTER LEDtube 1200mm UO 16W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	200000X
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 °
Luminous Flux (Nom)	2500 lm
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color Rendering Index (Nom)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	16 W
Lamp Current (Max)	75 mA
Lamp Current (Min)	68 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	35 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Efficiency Label (EEL)	A++


MASTER LEDtube EM/Mains T8

Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
Product Data	
Full product code	871869668740600
Order product name	MASTER LEDtube 1200mm UO 16W 865 T8

EAN/UPC - Product	8718696687406
Order code	929001298002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001298002
Net Weight (Piece)	0.251 kg

Warnings and Safety


Dimensional drawing




TLED 4ft 16W-36W 2500lm 160D 6500K G13ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm UO 16W 865 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data




LEDtube 1200mm UO 16W 865 T8



LEDtube 1200mm UO 16W 865 T8

MASTER LEDtube EM/Mains T8

Photometric data



LEDtube 600mm 1200mm 1500mm UO T8

Lifetime



LEDtube 600mm 1200mm 1500mm UO T8



LEDtube 600mm 1200mm 1500mm UO T8

