



MASTER LEDtube EM/ Mains

MASTER LEDtube 900mm HO 12W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime (nom.)	50000 h
Switching cycle	200000X

Light Technical	
Colour code	865 [CCT of 6,500 K]
Beam Angle (Nom)	160 °
Luminous flux (nom.)	1575 lm
Correlated colour temperature (nom.)	6500 K
Colour consistency	<6
Color rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	12 W
Lamp current (max.)	57 mA
Lamp current (min.)	51 mA
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V

Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product length	900 mm

Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes


MASTER LEDtube EM/Mains

Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	12 kWh
Product Data	
Full product code	871869668710900
Order product name	MASTER LEDtube 900mm HO 12W 865 T8
EAN/UPC – product	8718696687109

Order code	68710900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001298502
Net weight (piece)	0.174 kg

Warnings and Safety


Dimensional drawing




TLED 3ft 12W-30W 1575lm 160D 6500K G13ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 900mm HO 12W 865 T8	25.78 mm	28 mm	893.3 mm	900.4 mm	907.5 mm

Photometric data




LEDtube 600mm 1200mm 1500mm UO T8



LEDtube 900mm HO 12W865 T8


MASTER LEDtube EM/Mains

Photometric data




LEDtube 900mm HO 12W865 T8

Lifetime



LEDtube 600mm 1200mm 1500mm UO T8



LEDtube 600mm 1200mm 1500mm UO T8

