



MASTER LEDtube EM/ Mains

MASTER LEDtube 1200mm HO 14W830 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime (nom.)	50000 h
Switching cycle	200000X

Light Technical	
Colour code	830 [CCT of 3.000 K]
Luminous flux (nom.)	2000 lm
Luminous flux (rated) (nom.)	2000 lm
Correlated colour temperature (nom.)	3000 K
Colour consistency	<6
Color rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W
Lamp current (max.)	65 mA
Lamp current (min.)	60 mA
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V

Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	55 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product length	1200 mm

Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes


MASTER LEDtube EM/Mains

Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	14 kWh
Product Data	
Full product code	871869668724600
Order product name	MASTER LEDtube 1200mm HO 14W830 T8
EAN/UPC – product	8718696687246

Order code	68724600
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001299208
Net weight (piece)	0.215 kg

Warnings and Safety



Dimensional drawing



TLED 4ft 14W-36W 2000lm 150D 3000K G13ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm HO 14W830 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data




MAS LEDtube HO 14W G13 830 T8



MAS LEDtube HO 14W G13 830-865 T8

MASTER LEDtube EM/Mains

Photometric data





Lifetime



MAS LEDtube HO 14W G13 830-865 T8

MAS LEDtube HO 14W G13 830-865 T8




MAS LEDtube HO 14W G13 830-865 T8

MAS LEDtube HO 14W G13 830-865 T8

MASTER LEDtube EM/Mains

Lifetime



MAS LEDtube HO 14W G13 830-865 T8

