

PHILIPS

Eco passport

MASTER LEDtube HF 1500mm UO 24W840 T8 MASTER LEDtube InstantFit HF

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. The MASTER LEDtube Performance is the ideal solution for customers which have higher light requirements and the want to maximize value over lifetime.(need the longest lifetime). Full energy savings and TCO benefits.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** Yes
- **Energy Efficiency Label:** A++
- **Power (Rated) (Nom):** 24 W




Circularity

- **Nominal Lifetime (Nom):** 60000 h



Packaging

- **SAP Weight Paper Unit (Case):** 1.355 kg
- **SAP Weight Paper Unit (Piece):** 0.030 kg



Substances

- **EU REACH restrictions compliant:** Yes
- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes
- **PVC policy compliant:** Yes



Weight & Materials

- **Net Weight (Piece):** 0.450 kg

Further reading at:

<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2020 Signify Holding. All rights reserved.