

MASTER LEDtube HF 1500mm UO 24W865 T8

MASTER LEDtube InstantFit HF T8

Philips MASTER LEDtube InstantFit T8 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. Philips MASTER LEDtube InstantFit T8 is the ideal solution for customers who have higher light requirements and want to maximize value over lifetime. Full energy savings & longer lifetime result in attractive payback times and TCO benefits.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- Dimmable: No
- Energy Efficiency Label (EEL): A++
- Luminous Efficacy (rated) (Nom): 154.00 lm/W
- Power (Nom): 24 W



Circularity

- Nominal Lifetime (Nom): 60000 h



Packaging

- SAP Weight Paper Unit (Case): 1.355 kg
- SAP Weight Paper Unit (Piece): 0.030 kg



Substances

- EU REACH restrictions compliant: Yes
- EU REACH SVHC declaration: Yes
- EU RoHS compliant: Yes
- PVC policy compliant: Yes



Weight & Materials

- Net Weight (Piece): 0.450 kg

Energy efficiency ranking / External awards

