

PHILIPS

Eco passport

MASTER LEDtube HF 1500mm UO 24W830 T8 MASTER LEDtube InstantFit HF

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.



Our Eco passport



Energy

- Dimmable: Yes
- Energy efficiency label (EEL): A++
- Power (Rated) (Nom): 24 W




Circularity

- Nominal lifetime (nom.): 60000 h



Packaging

- SAP Weight Paper Unit (Case): 1.355 kg
- SAP Weight Paper Unit (Piece): 0.030 kg



Substances

- EU RoHS compliant: Yes
- RoHS mark: RoHS mark



Weight & Materials

- Net weight (piece): 0.450 kg

Energy efficiency ranking / External awards

