



T8

14T8/48-3000 IF 10/1 ROT

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data


General Information		Power Factor (Nom)		0.9	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)		120-277, 347 V	
EU RoHS compliant	Yes	Temperature			
Nominal Lifetime (Nom)	50000 h	T-Ambient (Max)		45 °C	
Switching Cycle	50000X	T-Ambient (Min)		-20 °C	
Light Technical		T-Storage (Max)		65 °C	
Color Code	830 [CCT of 3000K]	T-Storage (Min)		-40 °C	
Luminous Flux (Nom)	2000 lm	T-Case Maximum (Nom)		45 °C	
Correlated Color Temperature (Nom)	3000 K	Controls and Dimming			
Color Consistency	<6	Dimmable		No	
Color Rendering Index (Nom)	82	Mechanical and Housing			
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length		1200 mm	
Operating and Electrical		Approval and Application			
Input Frequency	50 to 60 Hz	Energy Saving Product		Yes	
Power (Nom)	14 W	Approval Marks		UL certificate RoHS compliance DLC compliance	
Starting Time (Nom)	0.5 s				
Warm Up Time to 60% Light (Nom)	0.5 s				
UL Type	Type A - works on ballast				

T8

Energy Certifications	DLC Standard
Product Data	
Order product name	14T8/48-3000 IF 10/1 ROT
EAN/UPC - Product	046677472689
Order code	929001303304

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001303304
Net Weight (Piece)	0.230 kg


Dimensional drawing




TLED 1200mm 120V 14-32W 2000lm 3000K G13

Product	D	D2	A1	A2	A3
14T8/48-3000 IF 10/1 ROT	25.68 mm	26.3 mm	1198 mm	1205 mm	1212 mm


Photometric data



LEDtube 1200mm 15W G13 T8 830 2000lm




LEDtube 1200mm 14-32W G13 830 2000lm




LEDtube 1200mm 14-32W G13 830 2000lm

Lifetime



LEDtube HF 1500mm 26W G5 T5



LEDtube 1200mm 14-32W G13

