



CorePro LEDbulbs

CorePro LED bulb ND 5-40W A60 E27 865


CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

Product data


| General Information | | Warm Up Time to 60% Light (Nom) | |
|---------------------------------------|---------------------|---------------------------------|---------------------------------------|
| Base | E27 [E27] | | 0.5 s |
| EU RoHS compliant | Yes | Power Factor (Nom) | 0.5 |
| Nominal Lifetime (Nom) | 15000 h | Voltage (Nom) | 220-240 V |
| Switching Cycle | 50000X | Temperature | |
| Technical Type | 5-40W | T-Case Maximum (Nom) | 75 °C |
| Light Technical | | Controls and Dimming | |
| Color Code | 865 [CCT of 6500K] | Dimmable | No |
| Beam Angle (Nom) | 200 ° | Mechanical and Housing | |
| Initial lumen (Nom) | 470 lm | Bulb Finish | Frosted |
| Color Designation | Cool Daylight | Approval and Application | |
| Correlated Color Temperature (Nom) | 6500 K | Energy Efficiency Label (EEL) | A+ |
| Luminous Efficacy (rated) (Nom) | 94.00 lm/W | Energy Consumption kWh/1000 h | 5 kWh |
| Color Consistency | <6 | Product Data | |
| Color Rendering Index (Nom) | 80 | Order product name | CorePro LED bulb ND 5-40W A60 E27 865 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | EAN/UPC - Product | 8718696577875 |
| Operating and Electrical | | Order code | 346155 |
| Input Frequency | 50 to 60 Hz | Numerator - Quantity Per Pack | 1 |
| Power (Rated) (Nom) | 5 W | Numerator - Packs per outer box | 10 |
| Lamp Current (Nom) | 48 mA | Material Nr. (12NC) | 929001304632 |
| Wattage Equivalent | 40 W | | |
| Starting Time (Nom) | 0.5 s | | |

CorePro LEDbulbs

Lifetime



LEDbulb 40W E27 830 FR A60



LEDbulb 40W E27 830 FR A60

