



Party Spot

13.5PAR38/PER/RED/ND/ULW/G/120V 4/1FB

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	Red
Color Designation	Red
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<6
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	13.5 W
Lamp Current (Nom)	165 mA
Wattage Equivalent	90 W
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	156 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Red
Bulb Material	Glass
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
EyeComfort	Yes
Product Data	
Order product name	13.5PAR38/PER/RED/ND/ULW/G/120V 4/1FB
Full product name	13.5PAR38/PER/RED/ND/ULW/G/120V 4/1FB

Party Spot

Order code	469106
Material Nr. (12NC)	929001306813
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677469108

Numerator - Packs per outer box	4
EAN/UPC - Case	50046677529890

