



MASTER LEDtube EM/ Mains

MAS LEDtube 600mm HO 8W830 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal Lifetime (Nom)	50000 h
Switching Cycle	200000X
B50L70	50000 h

Light Technical	
Colour Code	830 [CCT of 3000K]
Beam Angle (Nom)	160 °
Luminous Flux (Nom)	1000 lm
Luminous Flux (Rated) (Nom)	1000 lm
Rated Beam Angle	160 °
Colour Temperature, horizontal (Nom)	3000 K
Color Consistency	<6
Colour Rendering Index horiz (Nom)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	8 W

Lamp Current (Max)	42 mA
Lamp Current (Min)	36 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V

Temperature	
T-Ambient (Max)	35 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	600 mm

MASTER LEDtube EM/Mains

Approval and Application

Energy Efficiency Label	A++
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh

Product Data


Full product code	871869669747400
-------------------	-----------------

Order product name	MAS LEDtube 600mm HO 8W830 T8
EAN/UPC - Product	8718696697474
Order code	69747400
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001307002
Net Weight (Piece)	0.150 kg

Warnings and Safety

· -



Dimensional drawing



TLED 220-240V 8W-18W 1000lm 3000K G13

Product	D1	D2	A1	A2	A3
MAS LEDtube 600mm HO 8W830 T8	25.78 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


Photometric data



LEDtube 600mm HO 8W830 T8

MASTER LEDtube EM/Mains

Photometric data



Lifetime

