



# MasterClass LEDtube InstantFit T8

## 9T8 LED/36-3000 IF 10/1

The Masterclass LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h

Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	1100 lm
Luminous Flux (Rated) (Nom)	1100 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	20000-120000 Hz
Power (Nom)	9 W
Lamp Current (Max)	180 mA
Lamp Current (Min)	60 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.1 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277, 347 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	900 mm


Approval and Application	
Energy Efficiency Label (EEL)	Not applicable

# MasterClass LEDtube InstantFit T8

Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance
<b>Product Data</b>	
Order product name	9T8 LED/36-3000 IF 10/1
EAN/UPC - Product	046677472313
Order code	929001311304

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001311304
Net Weight (Piece)	0.170 kg



## Dimensional drawing



TLED 3ft 900mm 10.5-25W 1100lm 3000K ND


Product	D1	D2	A1	A2	A3
9T8 LED/36-3000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm

## Photometric data



LEDtube 900mm 9W G13 830 1100lm

LEDtube 600mm 7W G13



## MasterClass LEDtube InstantFit T8

### Lifetime



LEDtube 600mm 7W G13



LEDtube 600mm 7W G13

