



T8

13T8 LED/24-3500 IF-6U 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.1 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.9
Nominal Lifetime (Nom)	50000 h	Voltage (Nom)	120-277, 347 V
Switching Cycle	50000X	Temperature	
Light Technical		T-Ambient (Max)	45 °C
Color Code	835 [CCT of 3500K]	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	2000 lm	T-Storage (Max)	65 °C
Correlated Color Temperature (Nom)	3500 K	T-Storage (Min)	-40 °C
Color Consistency	<6	T-Case Maximum (Nom)	50 °C
Color Rendering Index (Nom)	82	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	No
Operating and Electrical		Mechanical and Housing	
Input Frequency	20000-120000 Hz	Product Length	600 mm
Power (Nom)	13 W	Approval and Application	
Lamp Current (Max)	165 mA	Energy Saving Product	Yes
Lamp Current (Min)	55 mA		
Starting Time (Nom)	0.5 s		


T8

Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-

Product Data	
Order product name	13T8 LED/24-3500 IF-6U 10/1
EAN/UPC - Product	046677472368

Order code	929001311904
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001311904
Net Weight (Piece)	0.270 kg



Dimensional drawing



TLED U bent U bent 13-32W 2000lm 3500K ND


Product	D1	D2	B	A1	D
13T8 LED/24-3500 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm

Photometric data





LEDtube 500mm 13W G13 835 2000lm

LEDtube 600mm 13W G13



LEDtube 500mm 13W G13 835 2000lm

Lifetime



LEDtube 600mm 7W G13

LEDtube 600mm 7W G13

