



MasterClass LEDtube InstantFit T8

13T8 LED/24-4000 IF-6U 10/1

The Masterclass LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	2100 lm
Luminous Flux (Rated) (Nom)	2100 lm
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	20000-120000 Hz
Power (Nom)	13 W
Lamp Current (Max)	165 mA
Lamp Current (Min)	55 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.1 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277, 347 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	600 mm
Approval and Application	
Energy Saving Product	Yes


MasterClass LEDtube InstantFit T8

Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-

Product Data	
Order product name	13T8 LED/24-4000 IF-6U 10/1

EAN/UPC - Product	046677472375
Order code	929001312004
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001312004
Net Weight (Piece)	0.270 kg


Dimensional drawing



TLED Ubent Ubent 13-32W 2100lm 4000K ND


Product	D1	D2	B	A1	D
13T8 LED/24-4000 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm

Photometric data




General Uniform Lighting
1.5m x 1.5m Area 1.5m x 1.5m Area
Page 10

LEDtube 500mm 13W G13 840 2100lm



LEDtube 600mm 13W G13



MasterClass LEDtube InstantFit T8

Lifetime



LEDtube 600mm 7W G13



LEDtube 600mm 7W G13

